
µGALV PRO – ELECTROPLATING SYSTEM


µGALV PRO – ELECTROPLATING SYSTEM

FOR INTENSIVE R&D TO PILOT PRODUCTION





45° flow plating



fountain plating



μGalvPro is a turn-key systems for electroplating, achieving excellent uniformity due to a 45° flowplating cell design and a rotating wafer holder. Process cells for various metals (Au, Ni, Cu) and alloys (Ni-Fe, Ni-Co, Ni-W, Sn-Pb) as well as additional rinsing cells or quick dump rinsers are

The µGalv Pro system is the ideal platform for electroplating applications from intensive R&D to pilot production.



Body	Material: standard PP white, optional PPs white, PVDF (with yellow card), elements CNC machined and welded
Operating Elements, electrical, regulation units, pneumatics	All process operating elements are integrated into the front panel, all electrical an pneumatically components are integrated in an independent compartment in the back side service area, DI- $\rm H_2O$ and $\rm N_2$ -Spray gun integrated in the workdeck.
Plating Modules	Overflow process consisting of a process cell and reserve tank with overflow/filtration circuit. Electroforming of pure metals like Ni, Cu, Au, Ag, Electroplating of alloy like NiFe, NiCo, NiW, SnPb Electro less plating of Ni, Au, SnPb Process cell configuration as rack plater, fountain tower or 45° flow channel (titled Wafer rotating) Depending on electrolyte, pH control (Acid and/or base) or cooling integrated Pulse plating with minimum pulse time of 0.10 msec
Wafer holder	PEEK, with stainless steel 1.4404 contact ring and gold plated wafer contacts, various edge excluisions available, min 3.5 mm edge exclusion
Cleaning Module	Standard Overflow-Rinser, optional Ultrasonic or Megasonic Cell cleaning module, optional QDR-module, optional SRD (Spin-Rinse-Dryer)
Process options	Process Cell with multiple process slots Basket handling in the case of electro less plating Pulse & reverse pulse rectifier with minimum pulse time of 0.1 msec



We want to ensure that we have close contact with our customers. If you have any questions or special requirements, please do not hesitate to get in touch with us. This product information sheet is for general information purposes only. The product descriptions and the content of this document are $\ \, \text{not a substitute for our instructions in the product manual}.$

Specifications contained in these pages are subject to ongoing change due to progress in research and development. AMMT reserves the right to update or modify any information without notice. This also applies to improvements and/or modifications to the products described herein. AMMT is not subject to should be subject to products or services. AMMT's product information sheets do not contain any representations or warranties. All technical specifications and price information are subject to change without notice.

AMMT GmbH — Advanced Micromachining Tools

Standard components	Valves: membrane valves, ball valves, different diameter Pump: centrifugal pump made of PP, optional PVDF Filter housing: PP 20", optional PVDF PP plumbing, optional PVDF or PFA tube 1/2", 3/4", 1" with PFA flaretek fittings Acess panel: touch panel display controller Remark: customized solutions available if requested
Other options	Automatic handling (semi auto, dry in – dry out) Integration of pre or post process cells possible Laminar-flow-units Vacuum twizer Quick connector fluid drain